

# Steam Hose for Humidifier



## Feature:

- Flexible Steam Hose for humidifiers

sold per foot  
part numbers not shown are non stock

# STEAM HOSE

Technical Data	2560052	2560053	2560054			
<b>Inside Diameter</b>	7/8" (22mm)	1-3/8" (35mm)	2-1/8" (54mm)	3-1/8" (80mm)	4-1/8" (100mm)	5-1/8" (125mm)
<b>Material</b>	Black EPDM with nylon reinforcement					
<b>Cover</b>	Garlock					
<b>Operating temperature</b>	-30°F to 250°F [0° C to 120° C]					
<b>Operation pressure</b>	150psi [1,000kPa]					
<b>Color</b>	White					

## Installation instructions

- Insert one end of the steam hose on the steam outlet of the evaporation chamber.
- Insert two hose clamps, one at the bottom of the hose secure the hose to the steam outlet.
- Insert a rigid length of steam line or connect to the steam distribution system at the other end of the steam hose and use the second hose clamp to secure the connection.